

17	16	26	Blade left 1	0	255	0.0%	100.0%	White → Full Blade left 1	0(0%)
		27		0	65535	0.0%	100.0%	Full Blade left 1, fine (LSB)	
18	17	28	Blade left 2	0	255	0.0%	100.0%	White → Full Blade left 2	0(0%)
		29		0	65535	0.0%	100.0%	Full Blade left 2, fine (LSB)	
19	18	30	Blade right 1	0	255	0.0%	100.0%	White → Full Blade right 1	0(0%)
		31		0	65535	0.0%	100.0%	Full Blade right 1, fine (LSB)	
20	19	32	Blade right 2	0	255	0.0%	100.0%	White → Full Blade right 2	0(0%)
		33		0	65535	0.0%	100.0%	Full Blade right 2, fine (LSB)	
21	20	34	Framing Rotation	0	255	0.0%	100.0%	Framing Rotation	0(0%)
		35		0	65535	0.0%	100.0%	Framing Rotation fine (LSB)	
22	21	36	Framing Rotation speed	0	255	0.0%	100.0%	Framing Rotation speed from slow to fast	0(0%)
23	22	37	Iris	0	255	0.0%	100.0%	Open → Close	0(0%)
24	23	38	Iris macro	0	31	0.0%	12.2%	Off / Open iris	0(0%)
				32	63	12.5%	24.7%	Effect - Synchronous open from slow to fast	
				64	95	25.1%	37.3%	Effect - Synchronous off	
				96	127	37.6%	49.8%	Effect - Random open from slow to fast	
				128	159	50.2%	62.4%	Effect - Random off	
				160	191	62.7%	74.9%	Strobe follow	
				192	255	75.3%	100.0%	Closed iris	
				0	255	0.0%	100.0%	Near → Far	
25	24	39	Focus	0	65535	0.0%	100.0%	Focus, fine (LSB)	0(0%)
26	25	41	Zoom	0	255	0.0%	100.0%	Narrow → Wide	0(0%)
27	26	43	Prism	0	31	0.0%	12.2%	Off	0(0%)
				32	255	12.5%	100.0%	On	
28	27	44	Prism rotation	0	127	0.0%	49.8%	Prism indexed	0(0%)
				128	187	50.2%	73.3%	Prism continous rotation CW from slow to fast	
				188	195	73.7%	76.5%	Stop	
				196	255	76.9%	100.0%	Prism continous rotation CCW from slow to fast	
29	28	45	Frost zoom	0	127	0.0%	49.8%	Off	0(0%)
				128	255	50.2%	100.0%	Frost zoom from smallest to biggest	
30	29	46	Pan	0	255	0.0%	100.0%	Pan	0(0%)
31		47		0	65535	0.0%	100.0%	Pan, fine (LSB)	
32	30	48	Tilt	0	255	0.0%	100.0%	Tilt	46(18.0%)
33		49		0	65535	0.0%	100.0%	Tilt, fine (LSB)	
34	31	50	Scan speed	0	255	0.0%	100.0%	Scan speed from slow to fast	0(0%)
35	32	51	Special controls	0	9	0.0%	3.5%	No function	0(0%)
				10	19	3.9%	7.5%	Open light after 5 seconds	
				20	29	7.8%	11.4%	Close light after 5 seconds	
				30	39	11.8%	15.3%	Color wheel half color switch	
				40	49	15.7%	19.2%	Color wheel random positioning	
				50	59	19.6%	23.1%	Blade motor reset after 5 seconds	
				60	69	23.5%	27.1%	Reset all motor after 5 seconds	
				70	79	27.5%	31.0%	Scan motor reset after 5 seconds	
				80	89	31.4%	34.9%	All color motor reset after 5 seconds	
				90	99	35.3%	38.8%	All gobo motor reset after 5 seconds	
				100	109	39.2%	42.7%	All strobe motor reset after 5 seconds	
				110	119	43.1%	46.7%	Other motor reset after 5 seconds	
				120	129	47.1%	50.6%	Built-in program 1	
				130	139	51.0%	54.5%	Built-in program 2	
				140	149	54.9%	58.4%	Built-in program 3	
				150	159	58.8%	62.4%	Built-in program 4	
				160	169	62.7%	66.3%	Built-in program 5	
				170	179	66.7%	70.2%	Built-in program 6	
				180	189	70.6%	74.1%	Built-in program 7	
				190	199	74.5%	78.0%	Built-in program 8	
				200	209	78.4%	82.0%	Built-in program 9	
				210	219	82.4%	85.9%	Built-in program 10	
				220	255	86.3%	100.0%	Voice control	